


HXYx

3 axes / ZL

● Arm type ● Cable carrier

● Z-axis: clamped base / moving table type (200W)



Ordering method

HXYx - C				ZL		
Model	Cable	Combination	X-axis stroke	Y-axis stroke	Z-axis stroke	Cable
A1			25 to 125cm	25 to 65cm	25 to 55cm	3L: 3.5m 5L: 5m 10L: 10m
A2						
A3						
A4						

RCX340-3								
Controller / Number of controllable axes	Safety standard	Option A (OP.A)	Option B (OP.B)	Option C (OP.C)	Option D (OP.D)	Option E (OP.E)	Absolute battery	
3L: 3.5m 5L: 5m 10L: 10m								

RCX240		R						
Controller	CE Marking	Regenerative unit	Expansion I/O	Network option	IVY System	Gripper	Battery	

Specify various controller setting items. RCX340 ▶ P494

Specify various controller setting items. RCX240/RCX240S ▶ P481

Specification

	X-axis	Y-axis	Z-axis
Axis construction Note 1	F20	F17	F14H-BK
AC servo motor output (W)	600	400	200
Repeatability Note 2 (mm)	+/-0.01	+/-0.01	+/-0.01
Drive system	Ball screw (Class C7)	Ball screw (Class C7)	Ball screw (Class C7)
Ball screw lead (Deceleration ratio) (mm)	20	20	10
Maximum speed Note 3 (mm/sec)	1200	1200	600
Moving range (mm)	250 to 1250	250 to 650	250 to 550
Robot cable length (m)	Standard: 3.5 Option: 5.10		

Note 1. Use caution that the flame machining (installation holes, tap holes) differs from single-axis robots'.

Note 2. Positioning repeatability in one direction.

Note 3. When the X-axis stroke is longer than 850mm, resonance of the ball screw may occur depending on the operation conditions (critical speed). In this case, reduce the speed setting on the program by referring to the maximum speeds shown in the table below.


Maximum payload

	250	350	450	550
Y stroke (mm)	20	20	20	20
250	20	20	20	20
350	20	20	20	20
450	20	20	19	18
550	18	17	16	15
650	18	17	16	15

Controller

Controller	Operation method
RCX340	Programming / I/O point trace / Remote command / Operation using RS-232C communication
RCX240-R	

HXYx 3 axes / ZL A1



X stroke	250	350	450	550	650	750	850	950	1050	1150	1250
L	667	767	867	967	1067	1167	1267	1367	1467	1567	1667
K	100	200	100	200	100	200	100	200	100	200	100
C	420	420	600	600	780	780	960	960	1140	1320	1320
M	2	2	3	3	4	4	5	5	6	6	7
N	8	8	10	10	12	12	14	14	16	16	18

Y stroke	250	350	450	550	650
Z stroke	250	350	450	550	

Maximum speed for each stroke (mm/sec) Note 3	X-axis	1200	960	840	720	600	480
Speed setting		-	80%	70%	60%	50%	40%

Note 1. The moving range when returning to origin and the stop position when stopping by the mechanical stopper.

Note 2. User cable extraction port.

Note 3. When the X-axis stroke is longer than 850mm, resonance of the ball screw may occur depending on the operation conditions (critical speed). In this case, reduce the speed setting on the program by referring to the maximum speeds shown in the table at the left.